


8000-422BMW WALL MOUNT for GENELLEC 6010A, 8020B, 8030A


black/white

Instruction Manual

1. Equipment




2. Separate speaker holder from wall plate



4. Wall mount fastening

4.a Adjust decorative plate according to the drilled two-or-three-hole-pattern




3. Wall mount preparation


3.a Determine wall fastening

- 3.a.1 Provided screw/dowel set is suitable for: concrete, full brick, perforated brick & drywall
- 3.a.2 For other walls like wood, adobe etc. use adequate anchors


3.b Adjust wall plate vertically and mark drilling holes (two options):




3.c Anchor holes drilling for two or three hole pattern: - dia. 8 mm



3.d Blow out holes and place anchors



4.b Bolt down the wall plate along with the decorative plate onto the wall. Use two or three screws depending on the prepared hole pattern




8000-422BW WALL MOUNT for GENELEC 6010A, 8020B, 8030A

black/white


Instruction Manual

5. Speaker installation

5.a
Bolt
speaker plate to
GENELEC speaker



5.b Replace the bolt of the speaker plate
(with mounted GENELEC)
into wall bracket




5.c Fix wall plate and
speaker bracket by tightening
lower bolted assembly

Safety Instructions

- Choose a position and mounting method compliant with local building codes and regulations
- For use only by trained installers
- For use only at proper walls with adequate anchors
- Not suitable are fragile walls.
- Beware of power supply lines and water conduits.
- In case ask an expert.
- Inspect bolted assemblies periodically
- For indoor use only

6. Settings (speaker-based)

6.a.1
tilting marks
30°
15°
30°
(no latching)




6.a - TILT ANGLE

Continuously adjustable tilting angles:

-up to 30-60° -down to 20-30°,
Fix both lateral allen screws (AF5 mm)


6.b.1
pivoting mark
centric adjustment
(no latching)



6.b - DIRECTION

Pivoting attachment
around vertical axis

7. Dimensions (in mm)



Weight: 0.5 kg

